


●●●●● 取扱説明書
 ●●●●● ブラケット
 ●●●●● **KRB500-PAD**

Part No. Z1-003-030, IA003103


Feb. 2008

次の手順で機器にブラケットを取付け、ラックに組み込みます。


1. 底部のキャスタ、および側面のねじを取り外します。




2. ④と⑤のねじを使用して①、②および③のブラケットを図のように取り付けます。
 ④のねじは、付属のねじ(M4 x 14皿ねじ)以外は使用しないでください。



3. ⑧のねじを使用して⑦のサポートアングルをラックのフレームへ取り付けます。
 図のように⑥のプレートを一列に貼り付けます。



4. ⑩のねじと⑨のワッシャを使用してラックに取り付けます。



NOTE

付属のサポートアングル(⑦)は、当社のラックKROシリーズ専用です。他のラックを使用する場合は、ラックに適合したサポートアングルを取り付けてください。

No.	コード	説明	数量
1	B9-000-107	BRKT KRB500-PAD (R)	1
2	B9-000-108	BRKT KRB500-PAD (L)	1
3	B9-000-084	BRKT TOP KRB500	1
4	M2-101-018	FLH SCREW S-NI M4X0.7X14	6
5	M2-101-009	FLH SCREW S-NI M3X0.5X8	2
6	Q3-000-062	PHENOL PLATE T0.5X15X360 KRB SERIES	2
7	D4-988-701	RAIL FOR EXTRA WEIGHT	2
8	M3-112-041	DBL SEMS K-MARU PNH SCR S-NI M5X0.8X10	8
9	M5-003-031	CUP WASHER 5 CW	8
10	M2-102-002	OVH SCREW S-NI M5X0.8X14	8



菊水電子工業株式会社


本社・技術センター 〒224-0023 横浜市都筑区東山田 1-1-3 TEL: 045-593-0200 (代)

INSTRUCTION MANUAL

Bracket KRB500-PAD


Install the brackets to the instrument in the next procedure and build in it to the rack.

1. Remove the casters on the bottom panel and the screws on the side panel.




2. As shown in figure, using ④ and ⑤ screws, install ①, ② and ③ brackets.


For ④ screws, do not use except the accompanying screws (M4 x 14 flat head screws).



3. Using ⑧ screws, install ⑦ support angles to the frame of the rack.
As shown in figure, stick ⑥ plates on the rails.



4. Using ⑩ screws and ⑨ washers, mount the instrument in the rack.



NOTE

The accompanying support angles (⑦) have been exclusively designed for the KRO series, KIKUSUI rack system. If you use other rack system, install the appropriate support angles applying to its rack system.

No.	CODE	DESCRIPTION	QTY
1	B9-000-107	BRKT KRB500-PAD (R)	1
2	B9-000-108	BRKT KRB500-PAD (L)	1
3	B9-000-084	BRKT TOP KRB500	1
4	M2-101-018	FLH SCREW S-NI M4X0.7X14	6
5	M2-101-009	FLH SCREW S-NI M3X0.5X8	2
6	Q3-000-062	PHENOL PLATE T0.5X15X360 KRB SERIES	2
7	D4-988-701	RAIL FOR EXTRA WEIGHT	2
8	M3-112-041	DBL SEMS K-MARU PNH SCR S-NI M5X0.8X10	8
9	M5-003-031	CUP WASHER 5 CW	8
10	M2-102-002	OVH SCREW S-NI M5X0.8X14	8



KIKUSUI ELECTRONICS CORP.

1-1-3, Higashiyamata, Tsuzuki-ku, Yokohama, 244-0023, Japan